



NIEUWKOOP

METEN.NL

LEAFLET



EP3050

EC-pH-ORP-ISE CONTROLLER



TO MEASURE  TO KNOW



The triple-measurement controllers EP3050 and EP3055 belong to the latest series of B&C Electronics/Nieuwkoop instruments and contain over 40 years of company experience in measuring and regulating electrochemical quantities using selective ion sensors (ISE), pH, redox and conductivity. The above mentioned sensors allow the simultaneous display of up to three measurements on the display in addition to the temperature measurement which also operates in automatic compensation. The flexibility of use of the various types of sensor makes the instrument suitable for many applications and types of system.

Main features

Inputs

The three inputs allow the selection of the following measurements:

Input A: conductivity/TDS/resistivity/indirect

Input B: ISE/pH/redox

Input C: ISE/pH/redox

Conductivity, TDS and resistivity scales

Cell K: 0.01- 0.1 - 0.5 - 1.0 - 10

from 200.0 nS to 2000 mS

from 100.0 ppb to 0.01 ppt

from 100 Mohm to 0.5 ohm

pH and redox scales

from 0.00 to 14.00 pH

from -2000 to +2000 mV

ISE scales

Ions: Cl⁻ NO₃⁻ NH₄⁺ Ca⁺⁺, others editable

from 0.01 to 1000 ppm, others editable

Temperature scales

from 0.0 to 100.0 °C

from 32.0 to 212.0 °F

Configuration

It can be configured for single measurement, double measurement or triple measurement.

Digital output

Isolated RS485 serial, with B&C ASCII protocol (text string) and Modbus RTU (03, 06, 16 function). Boot-loader function for firmware updates.

4 relays

Addressable for on-off adjustments, alarms, self-cleaning, automatic calibration or degassing.

PID adjustment

In PID adjustment via the analogue output, the level of the actuation is shown on the display. The user can select a PFM (pulse frequency) or PWM (pulse duration) addressed to the corresponding relay.

Alarms

Relay dedicated to these functions, settable on the min/max values of the measurements, the excessive permanence of the set points, the presence of the logic inputs, the failure of the automatic calibration or the exhaustion of the calibration solutions. Alternatively, this relay can be addressed and dedicated to the regulation function.

Logic inputs

Two independent dry contacts on closure that can create hold or alarm conditions.

Temperature compensation

It operates manually or automatically on pH, ISE, conductivity measurements.

Display

The graphic display shows all measurement values and guidance messages in the various phases of use, referring to the configured inputs.

Keyboards

The keys include those dedicated to zero and sensitivity calibration and set point setting.

Operating mode

Operation in automatic mode, measuring only or in the simulation mode for each input, in order to facilitate operations during start-up or maintenance of the system.

Two programmable software filters

They allow you to set values for small and large variations in order to obtain reading stability and speed of response to measurement variations in the process.

Two analogue outputs

Addressable on the inputs and programmable in the range 0/4 - 20 mA on two points of the measuring scale and they allow PID adjustment or transmission of measurement values.

Automatic calibration

Relay dedicated to the activation of an external system for automatic one-point or two-point calibration of ISE sensors.

Reagent consumption measurement

Measurement of reagent consumption for the automatic calibration of ISE sensors to prepare their refilling.

Universal power supply

Single-phase AC voltage from 85 to 264 V, 50-60 Hz. An option is available for use in DC voltage from 9 to 36 V or AC voltage from 12 to 24 V, 50-60 Hz.

Easy installation

EP3050 with IP66 protection, wall mounting, DIN rail mounting.
EP3055 with IP 65 front panel protection, panel mounting.

Compatible and versatile

The controller is compatible with any pH, redox and 2 or 4- electrode conductivity sensor. Monovalent or bivalent non pre-configured ISE sensors can be configured by the operator. Temperature measurement and compensation can be performed using a Pt100 or Pt1000 resistance thermometer with 2 or 3 wire connection.

Sensor cleaning

Programming software and relay dedicated to an external sensor self-cleaning device. Alternatively this relay can be addressed to the control function.



Applications

- Drinking water
- Aquaculture
- Food and beverage
- Chemical Industry
- Pharmaceutical Industry
- Textile Industry
- Fertirrigation
- Swimming pools
- Water Treatment

Technical specifications

Inputs:	2 or 4 electrode conductivity cells glass or antimony pH electrode redox electrode ISE electrodes Pt100 or Pt1000
Zero:	adjustable according to measure
Sensitivity:	adjustable according to measure
Resolution:	1 digit
Accuracy:	0.2 %
Repeatability:	0.1 %
Non linearity:	0.1 %
Dual filter software:	0.4 ÷ 50.0 seconds for small and large variations
Dual analog output:	0-20 mA / 4-20 mA Rmax 600 Ω
Digital output:	isolated RS485. B&C ASCII e Modbus RTU protocols (03, 06, 16 functions)
HI/LO set point:	ON/OFF - PID - PFM - PWM
Hysteresis:	0 ÷ 10 % of the scale
Delay:	0 ÷ 100.0 seconds
Alarm:	SPDT relay, 0 ÷ 100.0 seconds delay
Cleaning function:	off / autoclean / manual SPDT relay repetition time 0.1 ÷ 100.0 hours cleaning time 1.0 ÷ 60.0 seconds holding time 0.0 ÷ 20.0 minutes
Automatic calibration of the ISE electrodes:	1-point or 2-point, degassing
SPST and SPDT relay contacts:	220 Vac - 5 A resistive
Operating temperature:	-10 ÷ 60 °C
Humidity:	95% without condensation
Power supply:	85 ÷ 264 Vac - 50/60 Hz 9 ÷ 36 Vdc, 12 ÷ 24 Vac (091.42x option)
Terminal blocks:	removable
Net weight:	1360 g (EP3050) 450 g (EP3055)
Enclosure:	ABS, IP 66 protection (EP3050) metallic, IP 65 front panel (EP3055)
Dimensions:	256x230x89 mm (EP3050) 98x98x104 mm, 90x90x95 mm nel quadro (EP3055)
EMC/RFI conformity:	EN 61326
Ornamental design nbr.:	002564666-002 (EP3050) 002564666-003 (EP3055)



TO MEASURE  TO KNOW

Nieuwkoop BV

Aalsmeerderweg 249 -S
1432 CM AALSMEER

0297 325836

info@nieuwkoopbv.nl
www.meten.nl



NIEUWKOOP